# Reference Archive Media Data Sheet

# **KODAK Reference Archive Media 1433/3433**



# **Description**

Kodak Reference Archive Media has been specially formulated for use in the Kodak Imagelink i9600 Series Writers and the Kodak Digital Science™ Document Archive Writer, Model 4800, to provide high-quality, human-readable, reference archives of digital images.

The high-resolution archival-quality images are easily re-digitized for online access and retrieval to provide short-term validation and long-term storage of records. This media provides clear, high-contrast, and sharp images that can be distributed according to the requestor's needs as hard-copy output, faxes, or e-mail attachments, or posted to an image server using your current compression scheme. The requesting parties, whether users on your network or external customers or auditors, can then be directed to these images via links embedded in e-mails.

# **Product Applications**

Kodak Reference Archive Media and the i9600 Series Writers provide the easiest way to help protect your critical business records from tampering or loss. Reference Archive Media renders a trustworthy copy of an electronic record to validate a transaction that will satisfy litigation, and meet regulatory and audit requirements. These images can be used in reconstructing a record even if backup tapes, hardware, and software become obsolete.

You can avoid much of the expense and hazard of digital-only records storage by Reference Archiving critical business documents. Based upon technology developed by Kodak, Reference Archiving copies the records you wish to secure to an analog format on ISO-standard archival media. All of the information included in the original record is captured, in context. These non-volatile documents can be accessed electronically to authenticate current activities, such as an online transaction, or to support audit activities triggered by regulatory activities and legal actions. You can also be assured of long-term access and retrieval.

This media has a Life Expectancy of at least 500 years when processed and stored according to the recommended practices of ISO and ANSI.

#### **Media Features**

- Manufactured to ISO and ANSI standards for LE-500 films
- High resolution and excellent halation protection provide superior output of digital images
- Superior latent image keeping Minimal degradation of image density between time of exposure and delayed processing.
- · Process insensitive

Image quality and background density are not significantly affected by typical operational variations in processing.

 Roll-to-roll and emulsion batch-to-batch consistency

Minimizes the need for adjustments or operator intervention between rolls or batches of media.

Kodak Reference Archive Media is coated on polyester (PET) base, meeting ISO requirements for safety film (ISO 18906).

Process-surviving anti-static backing

Even after processing, static protection is maintained, reducing dirt and static problems in retrieval, scanning, and duplicating equipment.

#### **Physical Properties**

#### Nominal Thickness Data

Media	1433	3433		
Estar Base	5 mil (0.127 mm)	2.5 mil (0.064 mm)		
Emulsion	0.2 mil (0.005 mm)	0.2 mil (0.005 mm)		
Backing	Negligible*	Negligible*		
Total Mils**	5.2 (0.132 mm)	2.7 (0.069 mm)		

Static-resistant and process-survivable

#### **Photographic Properties**

**Spectral sensitivity:** Specially formulated to match the exposure device of the Kodak Digital Science Digital Document Archive System.

Resolving power: Based on recommended process.

Test-Object Contrast	Lines/mm		
1.6:1 (ISO-RPL)	200		
1000:1 (ISO-RP)	630		

These values were determined according to a method similar to ANSI/ISO 6328-1982, Photography—Photographic Materials— Determining the Resolving Power of Photographic Materials, Method for, except that the light source used was a high-pressure mercury arc.

#### **Process Handling and Storage**

#### Handling

Closed cartridges or film on standard flanged spools should be handled in subdued light. Subdued light may be used while loading and unloading the Kodak Digital Science Archive Writer Cassette, Model 66, for Reference Archive Media 3433 or a Kodak Imagelink Smart Cassette 100 for Reference Archive Media 1433.

Unprotected Kodak Reference Archive Media should be should be handled in total darkness. However, should a safelight be required for physical safety reasons, you can use a Kodak No. 3 Green Safelight Filter with a 7.5 watt bulb at a minimum of eight feet from the media. Packaged media may be handled in room light.

WARNING: This media may be handled under safelight conditions only for a limited time. Testing under actual use conditions should be done before taking this risk.

#### Media Storage Before Use

Keep unopened packages at 21°C (70°F), 50% relative humidity or below, and protected from radiation and X-rays. To avoid moisture condensation on media that has been refrigerated, do not open the package until the media has warmed throughout to normal room temperature, about 1 to 1 1/2 hours.

Before processing

# **Processor Setup Specifications for KODAK Reference Archive Media 3433**

	Developer		Fixer		Dryer	Dilution	
	Time (sec.)	Temperature	Time (sec.)	Temperature	Temperature	Dev	Fix
Kodak Prostar	13.5	100°F (37.8°C)	13.5	96°F (35.6°C)	135°F (57.2°C)	RTU*	RTU*
Medium Tank**	23	90°F (32.2°C)	23	85°F (29.4°C)	160°F (71.1°C)	1:2	1:2
Deep Tank**	48	85°F (29.4°C)	32	85°F (29.4°C)	160°F (71.1°C)	1:7	1:3

<sup>\*</sup> RTU = Ready To Use

#### **Processing Information**

#### **Processors**

Kodak Reference Archive Media can be processed in most typical continuous-strand type Kodak Prostar, medium-tank, and deep-tank processors.

#### **Processing Chemicals**

Kodak Reference Archive Media has been designed and tested to yield optimum results utilizing common Kodak Processing Chemicals and parameters. However, it is compatible with other standard microfilm processing equipment and high quality chemicals (results may vary).

IMPORTANT: For best results and to avoid aeration, always add chemical concentrate to water, not water to concentrate

#### **Replenishment Rates**

Use the chart and formula provided to determine the developer and fixer replenishment rates (mL/min) by multiplying transport speed (ft/min) (which is determined by dividing the path length of the developer tank in feet by the dwell time in seconds and multiplying by 60; see example) and the appropriate processor replenishment specification (mL/linear foot).

Replenishment Specification (mL/linear ft)			
	16 mm		
Type of Processor	Dev	Fix	
Kodak Prostar	0.75	0.75	
Mediumtank	0.80	0.75	
Deep tank	1.00	1.25	

Transport Replenishment/ Replenishment speed x ft of film = rate (ft/min) (mL/Lft) (mL/min\*)

\*1 mL/min = 1 cc/min

# Example

Processor: Allen M70
Type of film: 16 mm
Dwell: 43 seconds
Developer film path: 154 feet

See table above for:

Replenishment (Dev): 1 Replenishment (Fix): 1.25

Calculated transport speed:

$$\frac{154 \text{ feet x } 60 \text{ sec}}{43 \text{ sec}} = 215 \text{ ft / min}$$

#### Replenishment results:

$$\frac{215 \text{ feet}}{\text{min}} \frac{\text{x } 1.0 \text{ mL}}{\text{feet}} = 215 \text{ mL / min*}$$
(developer replenishment)

A bluish tint in the background is a normal postprocess characteristic of this media. Extreme variations from the recommended processing conditions will affect the severity of the tint. This characteristic does not negatively affect image permanence, quality, or reproducibility.

<sup>\*\*</sup> NOTE: The above dwell times and temperatures are starting points only. Specific systems or customer needs may demand variation from these values based on photographic aims. Dwell time is determined by timing media speed from entrance roller to exit roller while running in the processor.

#### Image Stability—Post-Processing

This media is manufactured to ANSI and ISO specifications for extended-term storage use. When processed as recommended, this media meets both ANSI and ISO specifications intended for long-term storage. This media has a Life Expectancy LE-500 rating.

ISO 18901:2002, Photography—Processed Silver-Gelatin Type Black-and-White Film—Specifications for Stability, states that the maximum permissible concentration of thiosulfate ion is 0.014 grams per square metre for extended-term storage. ISO 18901 has superceded ANSI/NAPM IT9.1-1992. Requirements have not changed.

#### Media Keeping—Post-Processing

ISO 18911-2000, *Photography—Processed Safety Photographic Films Storage Practices*, give appropriate conditions for extended-term (permanent) and long-term storage. These are the same requirements as previously stated in ANSI/NAPMIT9.11-1993.

Obtain these ANSI and ISO Standards through one of these ways:

 Contact the Association for Information and Image Management International (AIIM):

http://www.aiim.org

or

1100 Wayne Avenue, Suite 1100 Silver Spring, MD 20910-5603


- Call 1-301-587-8202
- Visit the American National Standards Institute (ANSI) Internet web site:

http://www.ansi.org

NOTE: Refer to the latest revision of each ANSI or ISO Standard specified.

# **BEO\*** Intensity vs. Density






<sup>\*</sup> BEO = Brightness Emitter Optimization—a measure of the light intensity of the LEDs, which is controlled by the amount of time the LEDs are on.

**Notice:** While the data presented are typical of production coatings, they do not represent standards which must be met by Eastman Kodak Company. Varying storage, exposure, and processing conditions will affect results. The company reserves the right to change and improve the product characteristics at any time.


#### **Characteristic Curve**

Kodak Reference Archive Media
Kodak Prostar Processor and Kodak Prostar Plus Chemicals



# **Spectral Sensitivity Curve**

Kodak Reference Archive Media 1433, 3433
Xenon Flash exposure, 85 microseconds, KODAK WRATTEN 29 Filter:
Kodak Prostar Processor and Kodak Prostar Plus Chemicals



#### Ordering Information: Reference Archive Media

Code	Mil	Format	Spec	Desc	No./Case	CAT No.
1433	5	16 mm x 100 ft	615	R-186 Black plastic spool*	20	153-4601
3433	2.5	16 mm x 215 ft	615	R-186 Black plastic spool**	20	862-5147

<sup>\*</sup> Uses Kodak Imagelink Smart Cassette 100, CAT No. 153-7166

#### **Ordering Information: Chemicals**

Chemical	CAT Number	Working Strength Solutions	
Microfilm DEVELOPER AND Repler	At 1:7 yields		
1 gal—4/case	177-8869	32 gal	
5 gal—1 cube	190-1891	40 gal	
50 gal—1 drum	190-1917	400 gal	
Microfilm FIXER AND Replenisher-	At 1:3 yields		
1 gal—4/case	817-7222	16 gal	
5 gal—1 cube	190-1149	20 gal	
50 gal—1 drum	190-1164	200 gal	
Kodak Prostar Processors	Ready-to-Use Solution		
<b>Prostar</b> Plus Developer 1 gal 4/case	102-2490	4 gal	
<i>Prostar</i> Plus Fixer 1 gal 4/case	102-2656	4 gal	

Material Safety Data Sheets (MSDSs) on the chemicals (only) are available by contacting Kodak at 1-800-242-2424 or www.kodak.com/go/msds. You will need to supply the *Kodak* catalog numbers of the chemicals for which you need MSDSs. Material Safety Data Sheets for the actual working solutions and caution labels for the processor tanks are also available by calling the same number.

#### **READ THIS NOTICE**

The sensitometric curves and data in this publication represent product tested under the conditions of exposure and processing specified. They are representative of production coatings and, therefore, do not apply directly to a particular box or roll of photographic material. They do not represent standards or specifications which must be met by Eastman Kodak Company. The company reserves the right to change and improve product characteristics at any time.

EASTMAN KODAK COMPANY Document Imaging Rochester, NY 14650 1-800-243-8811

KODAK CANADA INC.
Document Imaging
Toronto, Ontario M6M 1V3
1-800-465-6325

Kodak, Digital Science, Estar, and Prostar are trademarks.

www.kodak.com/go/docimaging

Kodak Reference Archive Media 1433/3433 Kodak Publication No. D-35 CAT No. 859-9342 3/2003 Printed in U.S.A. © Eastman Kodak Company, 2003



<sup>\*\*</sup> Uses Kodak Digital Science Archive Writer Cassette, Model 66, CAT No. 868-4383